






- MILITARY STANDARD
- 3106 STYLE
- INSERT ARRANGEMENT 22–14S
- SOLID BACKSHELL
- MAX DIAMETER 1.468 IN.

- JACKET:
- SOOW CABLE
  - 3 CONDUCTOR, 16 AWG
  - TEMPERATURE RANGE: −40°C TO 90°C
- INDUSTRY APPROVALS:
- UL FLEXIBLE CORD UL SUBJECT 62
  - CSA FLEXIBLE CORD C22.2–49
  - MSHA APPROVED
  - ROHS COMPLIANT

- MILITARY STANDARD
- 3106 STYLE
- INSERT ARRANGEMENT 18–11S
- SOLID BACKSHELL
- MAX DIAMETER 1.22 IN.



CONNECTOR PIN	WIRE COLOR	WIRE TYPE	FUNCTION		CONNECTOR PIN
C	BLACK	#16 AWG 26/30 STRAND	PHASE 1	OPEN	D
D	GREEN	#16 AWG 26/30 STRAND		CLOSE	C
E	WHITE	#16 AWG 26/30 STRAND		COMMON	B
F	BLACK	#16 AWG 26/30 STRAND	PHASE 2	OPEN	D
G	GREEN	#16 AWG 26/30 STRAND		CLOSE	C
H	WHITE	#16 AWG 26/30 STRAND		COMMON	B
J	BLACK	#16 AWG 26/30 STRAND	PHASE 3	OPEN	D
K	GREEN	#16 AWG 26/30 STRAND		CLOSE	C
L	WHITE	#16 AWG 26/30 STRAND		COMMON	B