


CONNECTOR PIN	WIRE COLOR	WIRE TYPE	FUNCTION		CONNECTOR PIN
J1-A	BLACK	#12 AWG 65/30 STRAND	POWER SUPPLY	120 VAC	WIRE TERMINATION
J1-B	WHITE	#12 AWG 65/30 STRAND		NEUTRAL	WIRE TERMINATION
J1-E	WHITE	#16 AWG 26/30 STRAND	PHASE 1	PHASE 1 COMMON	J2-B
J1-D	GREEN	#16 AWG 26/30 STRAND		PHASE 1 CLOSE	J2-C
J1-C	BLACK	#16 AWG 26/30 STRAND		PHASE 1 OPEN	J2-D
J1-U	RED	#16 AWG 26/30 STRAND		PHASE 1 COMMON	J2-E
J1-N	ORANGE	#16 AWG 26/30 STRAND		PHASE 1 52b	J2-F
J1-M	BLUE	#16 AWG 26/30 STRAND		PHASE 1 52a	J2-G
J1-H	WHITE	#16 AWG 26/30 STRAND		PHASE 2 COMMON	J3-B
J1-G	GREEN	#16 AWG 26/30 STRAND	PHASE 2	PHASE 2 CLOSE	J3-C
J1-F	BLACK	#16 AWG 26/30 STRAND		PHASE 2 OPEN	J3-D
J1-U	RED	#16 AWG 26/30 STRAND		PHASE 2 COMMON	J3-E
J1-R	ORANGE	#16 AWG 26/30 STRAND		PHASE 2 52b	J3-F
J1-P	BLUE	#16 AWG 26/30 STRAND		PHASE 2 52a	J3-G
J1-L	WHITE	#16 AWG 26/30 STRAND	PHASE 3	PHASE 3 COMMON	J4-B
J1-K	GREEN	#16 AWG 26/30 STRAND		PHASE 3 CLOSE	J4-C
J1-J	BLACK	#16 AWG 26/30 STRAND		PHASE 3 OPEN	J4-D
J1-U	RED	#16 AWG 26/30 STRAND		PHASE 3 COMMON	J4-E
J1-T	ORANGE	#16 AWG 26/30 STRAND		PHASE 3 52b	J4-F
J1-S	BLUE	#16 AWG 26/30 STRAND		PHASE 3 52a	J4-G




• MILITARY STANDARD
• 3106 STYLE
• INSERT ARRANGEMENT 22-14S
• SOLID BACKSHELL
• MAX DIAMETER 1.468 IN.



JACKET:
• SOOW CABLE
• 6 CONDUCTOR, 16 AWG
• TEMPERATURE RANGE: -40°C TO 90°C

INDUSTRY APPROVALS:
• UL FLEXIBLE CORD UL SUBJECT 62
• CSA FLEXIBLE CORD C22.2-49
• MSHA APPROVED
• ROHS COMPLIANT

• MILITARY STANDARD
• 3106 STYLE
• INSERT ARRANGEMENT 16S-1S
• SOLID BACKSHELL
• MAX DIAMETER 1.22 IN.



• SHIELDED SOOW CABLE
• UL STANDARD 62
• UL AND CSA LISTED
• TEMPERATURE RATING 90°C
• VOLTAGE RATING: 600V
• 2 CONDUCTOR, 12 AWG