


CONNECTOR PIN	WIRE COLOR	WIRE TYPE	FUNCTION		CONNECTOR PIN
J1-J	RED	#16 AWG 26/30 STRAND	PHASE 1	●IA	J2-A
J1-K	WHITE	#16 AWG 26/30 STRAND		IN	J2-B
J1-E	GREEN	#16 AWG 26/30 STRAND		VA	J2-C
J1-H	BLACK	#16 AWG 26/30 STRAND		VN	J2-D
J1-L	RED	#16 AWG 26/30 STRAND	PHASE 2	●IB	J3-A
J1-M	WHITE	#16 AWG 26/30 STRAND		IN	J3-B
J1-F	GREEN	#16 AWG 26/30 STRAND		VB	J3-C
J1-H	BLACK	#16 AWG 26/30 STRAND		VN	J3-D
J1-N	RED	#16 AWG 26/30 STRAND	PHASE 3	●IC	J4-A
J1-P	WHITE	#16 AWG 26/30 STRAND		IN	J4-B
J1-G	GREEN	#16 AWG 26/30 STRAND		VC	J4-C
J1-H	BLACK	#16 AWG 26/30 STRAND		VN	J4-D

- MILITARY STANDARD
- 3106 STYLE
- INSERT ARRANGEMENT 22-19S
- SOLID BACKSHELL
- MAX DIAMETER 1.560 IN.



- XTRA GUARD 2
- 4 CONDUCTOR, 16 AWG
- TEMPERATURE RANGE: -20°C TO 80°C

- MILITARY STANDARD
- 3106 STYLE
- INSERT ARRANGEMENT 14S-2P
- SOLID BACKSHELL
- MAX DIAMETER 1.44 IN.

