










- MILITARY STANDARD
- 3106 STYLE
- INSERT ARRANGEMENT 22-19S
- SOLID BACKSHELL
- MAX DIAMETER 1.56 IN.

- JACKET:
- EXTRA GUARD II
 - 4 CONDUCTOR, 16 AWG SHIELDED
 - TEMPERATURE RANGE: -20°C TO 90°C
- INDUSTRY APPROVALS:
- UL FLEXIBLE CORD UL SUBJECT 62
 - CSA CABLE STYLE: AWM SR-PVC 80 C
 - UL CABLE STLE: 20233

- MILITARY STANDARD
- 3106 STYLE
- INSERT ARRANGEMENT 16S-1P
- SOLID BACKSHELL
- MAX DIAMETER 1.25 IN.



CONNECTOR PIN	WIRE COLOR	WIRE TYPE	FUNCTION		CONNECTOR PIN
J1-E	RED	#16 AWG 26/30 STRAND	PHASE 1	VA	J2-A
J1-H	GREEN	#16 AWG 26/30 STRAND		VN	J2-F
J1-J	BLACK	#16 AWG 26/30 STRAND		1A+	J2-D
J1-K	WHITE	#16 AWG 26/30 STRAND		1A-	J2-C
J1-A	DRAIN	#16 AWG 26/30 STRAND		GND	J2-E
J2-G	RED	#20 AWG	JUMPER		J2-B
		#20 AWG	JUMPER		
J1-F	RED	#16 AWG 26/30 STRAND	PHASE 2	VB	J3-A
J1-H	GREEN	#16 AWG 26/30 STRAND		VN	J3-F
J1-L	BLACK	#16 AWG 26/30 STRAND		1B+	J3-D
J1-M	WHITE	#16 AWG 26/30 STRAND		1B-	J3-C
J1-A	DRAIN	#16 AWG 26/30 STRAND		GND	J3-E
J3-G	RED	#20 AWG	JUMPER		J3-B
		#20 AWG	JUMPER		
J1-G	RED	#16 AWG 26/30 STRAND	PHASE 3	VC	J4-A
J1-H	GREEN	#16 AWG 26/30 STRAND		VN	J4-F
J1-N	BLACK	#16 AWG 26/30 STRAND		1C+	J4-D
J1-P	WHITE	#16 AWG 26/30 STRAND		1C-	J4-C
J1-A	DRAIN	#16 AWG 26/30 STRAND		GND	J4-E
J4-G	RED	#20 AWG	JUMPER		J4-B
		#20 AWG	JUMPER		