


CONNECTOR PIN	WIRE COLOR	WIRE TYPE	FUNCTION		CONNECTOR PIN
J1-A	BLACK	#12 AWG 65/30 STRAND	POWER SUPPLY	120 VAC	WIRE TERMINATION
J1-B	WHITE	#12 AWG 65/30 STRAND		NEUTRAL	WIRE TERMINATION
J1-C	BLACK	#16 AWG 26/30 STRAND		OPEN	J2-3
J1-D	WHITE	#16 AWG 26/30 STRAND		CLOSE	J2-4

- MILITARY STANDARD
- 3106 STYLE
- INSERT ARRANGEMENT 22-10
- SOLID BACKSHELL
- MAX DIAMETER 1.869 IN.

- JACKET:
- SOOW CABLE
 - 3 CONDUCTOR, 16 AWG
 - TEMPERATURE RANGE: -40°C TO 90°C
- INDUSTRY APPROVALS:
- UL FLEXIBLE CORD UL SUBJECT 62
 - CSA FLEXIBLE CORD C22.2-49
 - MSHA APPROVED
 - ROHS COMPLIANT

- SHIELDED SOOW CABLE
- UL STANDARD 62
- UL AND CSA LISTED
- TEMPERATURE RATING 90°C
- VOLTAGE RATING: 600V
- 2 CONDUCTOR, 12 AWG



CABLE ASSY, 4-PIN TO 2-PIN AND 2-COND		DATE	
SCALE	ENGINEER	DRAWN	DATE
NTS	S. COLLIGAN	D. HAMILTON	8/14/13
DWG NO.	LDWC539	SHT	REV
		1	A

SEL SCHWEITZER ENGINEERING LABORATORIES	
PULLMAN WASHINGTON USA	
This drawing was prepared for a specific project and is not to be used for any other purpose without the written permission of SEL and the customer.	

DESCRIPTION		APPROVAL	DATE	REV. NO.
INITIAL DRAFT		D. HAMILTON	8/14/13	A