

SEL-321-0,-1, -2,-3,-4



2350 NE Hopkins Court • Pullman, WA 99163-5603 USA
 Phone: (509) 332-1890 • Fax: (509) 332-7990
 Internet: www.selinc.com • E-mail: info@selinc.com

Phase and Ground Distance Relay
 Directional Overcurrent Relay
 Standard with Conventional
 Terminal Blocks



Ordering Information

Note: This is a two-page document.

Part Number Example: 321224255HGB554

Choose from the following options.
 Enter option codes to complete the part number.

3 2 1

Page 1					Page 2				

Enter option codes from page 2 in the shaded spaces above.

Firmware

ASCII Communications	0																			
ASCII, Compressed ASCII, Fast Meter, Fast Operate, MIRRORING BITS™	1																			
SEL-321-1 plus 300 Cycle Event Reports	* 2																			
SEL-321-1 and DNP 3.0 Level 2 Slave plus Dialout and Virtual Terminal	* 3																			
SEL-321-3 plus expanded memory for up to twenty 12-cycle event reports	* 4																			

Chassis⁽¹⁾

One I/O Board, 3U	1																			X
Two I/O Boards, 4U	* 2																			
Two I/O Boards, IP50, 4U	* A																			
Two I/O Boards, IP50/54 (IP54 protected front only, must be panel mounted), 4U	* B																			

Power Supply

24/48 Vdc	2																			
48/125 Vdc or 125 Vac	3																			
125 Vdc or Vac	4																			
250 Vdc or Vac	6																			

Secondary Input Voltage; Current^{(1), (2)}

67 Vac Phase-Neutral; 1 Amp Phase	2	1																		
67 Vac Phase-Neutral; 5 Amp Phase	2	5																		
67 Vac Phase-Neutral; 100 mV (electronic level input) Phase	2	A																		X
67 Vac Phase-Neutral; 200 mV (electronic level input) Phase	2	B																		X
1.314 Vac (electronic level input) Phase-Neutral; 100 mV (electronic level input) Phase	A	A																		X
4 Vac (electronic level input) Phase-Neutral; 150 mV (electronic level input) Phase	C	C																		X

Frequency

50 Hz																				5
60 Hz																				6

Mounting

Horizontal Rack Mount																				H
Vertical Rack Mount																				V

* Additional Cost

⁽¹⁾ 2 or more option codes per line are grouped and must be entered together.

⁽²⁾ Additional I/O boards are not available in SEL-321 Relays with Electronic Level Inputs.

Note: The SEL-321-0, -1, -2, -3, -4 comes standard with a CD manual. A hard copy instruction manual is available upon request.

