

SEL-351-0Y, -1Y, -2Y, -3Y, -4Y Connectorized®

Overcurrent Protection System
Standard with 8 Outputs, 6 Inputs
Plug-In Connectors

Ordering Information⁽²⁾



2350 NE Hopkins Court • Pullman, WA 99163-5603 USA
Phone: (509) 332-1890 • Fax: (509) 332-7990
Internet: www.selinc.com • E-mail: info@selinc.com

Note: This is a two-page document.

Choose from the following options.
Enter option codes to complete the part number.

0 3 5 1

Page 1				Page 2			
	Y					X	

Enter option codes from page 2 in the shaded spaces above.

Firmware; Secondary Input Voltage⁽¹⁾

Standard; with 150 Vac Phase-Neutral Maximum (Wye)	0				2				
Standard; with 300 Vac Phase-Phase Maximum (Delta)	0				3				
Standard plus MIRRORRED BITS™, Load Profile; with 150 Vac Phase-Neutral Maximum (Wye)	1				2				
Standard plus MIRRORRED BITS, Load Profile; with 300 Vac Phase-Phase Maximum (Delta)	1				3				
Standard plus MIRRORRED BITS, Load Profile, Power Elements; with 300 Vac Phase-Neutral Maximum (Wye)	*	2			5				
Standard plus MIRRORRED BITS, Load Profile, Voltage Sag/Swell/Interruption; with 300 Vac Phase-Neutral Maximum (Wye)	*	3			5				
Standard plus MIRRORRED BITS, Load Profile, Voltage Sag/Swell/Interruption, Power Elements; with 300 Vac Phase-Neutral Maximum (Wye)	*	4			5				

I/O Board; Chassis⁽¹⁾

No Additional I/O, 3U				Y					X
Additional 12 Std Outputs, 8 Inputs, 3U (only 4 outputs configurable, Form A or Form B)	*			Y					2
Additional 12 High I/C Outputs, 8 Inputs, 3U (only 4 outputs configurable, Form A or Form B)	*			Y					6

Mounting

Horizontal Rack Mount					H				
Horizontal Panel Mount					3				
Horizontal Projection Panel Mount	*				5				
Vertical Rack Mount					V				
Vertical Panel Mount					4				

Power Supply

24/48 Vdc					2				
48/125 Vdc or 125 Vac					3				
125/250 Vdc or Vac					4				

Secondary Input Current

1 Amp Phase, 1 Amp Neutral									1
5 Amp Phase, 5 Amp Neutral									5
5 Amp Phase, 1 Amp Neutral									6
1 Amp Phase, 0.05 Amp Neutral (select for Sensitive Earth Fault detection)									8
5 Amp Phase, 0.05 Amp Neutral (select for Sensitive Earth Fault detection)									9

* Additional Cost

⁽¹⁾ Two or more option codes per line are grouped and must be entered together.

⁽²⁾ Specify wiring harness WA0351 using order form WI-1027.

Note: The SEL-351-0Y,-1Y,-2Y,-3Y,-4Y Connectorized® comes standard with a CD manual. A hard copy instruction manual is available upon request.

Not Recommended for New Design. SEL-351-5Y, -6Y, -7Y Connectorized is recommended for use in place of the SEL-351-0Y, -1Y, -2Y, -3Y, -4Y Connectorized.

