




SEL-2488 Satellite-Synchronized Network Clock

Advanced Time Synchronization



Key Features and Benefits

The SEL-2488 Satellite-Synchronized Network Clock receives Global Navigation Satellite System (GNSS) time signals and distributes precise time via multiple output protocols, including IRIG-B, Precision Time Protocol (PTP) as defined by IEEE 1588-2008, and Network Time Protocol (NTP). The advanced capabilities of the SEL-2488 make it well suited for demanding applications like synchrophasors and for substations with multiple time synchronization requirements.

- **Precise Time Accuracy Meets Demanding Requirements.** Provides demodulated IRIG-B time output for protection applications, synchronizing relays, phasor measurement units (PMUs), and other intelligent electronic devices (IEDs) to within ± 40 ns average and ± 100 ns peak accuracy to coordinated universal time (UTC). The SEL-2488 can act as a stratum 1 time server with typical client synchronization accuracy on a LAN of 0.5–2 ms. With purchase of the PTP option, the SEL-2488 can act as a PTP Grandmaster Clock providing ± 100 ns peak time stamp accuracy to UTC.
- **Holdover Oscillator Maintains Accuracy if GPS is Unavailable.** Maintains average accuracy of 36 μ s after 24 hours at constant temperature with standard Temperature Compensated Crystal Oscillator (TCXO) holdover. With optional Oven Controlled Crystal Oscillator (OCXO) holdover, average accuracy improves to 5 μ s after 24 hours at constant or varied temperature.
- **Thirteen Standard Outputs Provide Flexible Time Distribution.** Distributes time from eight time BNC outputs plus one DB-9 output, all configurable for IRIG-B or time pulse outputs. The DB-9 port can be used with SEL-2812 Fiber-Optic Transceivers With IRIG-B or SEL-3405 High-Accuracy IRIG-B Fiber-Optic Transceivers to send IRIG-B over long distances via a fiber-optic cable. The SEL-2488 also includes four standard Ethernet ports, which provide NTPv4. With purchase of the PTP option, the SEL-2488 can act as a PTP Grandmaster Clock (IEEE 1588-2008) with Default (Annex J), Power System (IEEE C37.238-2011/2017), and Power Utility Automation (IEC/IEEE 61850-9-3:2016) profiles. The SEL-2488 distributes NTP and PTP to four independent networks, and Ethernet ports are available in copper as well as single- or multimode fiber orderable in pairs.
- **Dual Power Supplies Offer Redundancy.** Provides an option for a second power supply that can receive power from a second source. SEL-9330-A power supplies support 125–250 Vdc or Vac input, and SEL-9330-C power supplies use 24–48 Vdc.
- **Satellite Signal Verification (SSV) Provides Assurance.** Receives signals from both GPS and GLONASS satellite systems for verification to provide a level of protection from GPS spoofing attacks.
- **DHCP, LDAP, SNMP, and Syslog Support Ensure Easy and Secure Integration.** Makes commissioning, management, and monitoring faster and more secure with DHCP Captive Port, LDAP authentication, SNMP read and trap support, and syslog event messaging.
- **Doubly Attached Node Implementing PRP (DANP) Support Provides Network Redundancy.** Supports as many as two DANP interfaces that use all four rear-panel physical Ethernet ports, allowing a connection to two separate PRP networks without requiring PRP Redboxes. Each DANP interface supports PTP over PRP as a Doubly Attached Clock (DAC) device. The SEL-2488 complies with the IEC 62439-3:2016 standard.
- **Active-Backup Port Bonding Provides Ethernet Failover.** Active-backup port bonding logically combines two physical Ethernet ports into a single network interface with only one port active while the other serves as a failover backup. The SEL-2488 supports as many as two independent active-backup bonded interfaces that use the four rear-panel physical Ethernet ports.

- **Ruggedness Provides Reliability in Harsh Environments.** Operates reliably between -40° and $+85^{\circ}\text{C}$ (-40° to $+185^{\circ}\text{F}$), and complies with IEEE 1613, IEC 61850-3, and IEC 60255 standards.
- **Easy-to-Use Interface Streamlines Device Management.** The intuitive SEL-2488 HTTPS device webpage with SkyView[®] simplifies configuration, management, and troubleshooting.

Functional Overview




Figure 1 Functional Diagram

The SEL-2488 raises the bar for satellite-synchronized clocks by providing higher levels of accuracy, flexibility, dependability, and ease of use, all while providing advanced capabilities that make it especially well suited for critical infrastructure applications.

Standard Features

- Average accuracy of ± 40 ns to UTC, peak accuracy of ± 100 ns to UTC for demodulated IRIG-B and pulse outputs
- Time sources used: GPS, GLONASS for satellite signal verification
- Typical NTP time-stamp accuracy < 100 μs
- Peak PTP time-stamp accuracy of ± 100 ns to UTC
- Peak accuracy of ± 1 μs to UTC for modulated IRIG-B
- Standard TCXO holdover with 36 μs average timing error after 24 hours at constant temperature
- Optional OCXO holdover with 5 μs average timing error after 24 hours at constant or varied temperature
- Eight rear BNC ports for demodulated IRIG-B, PPS, or kPPS, and as many as four ports for modulated IRIG-B
- Four Ethernet ports can serve NTPv4 and PTP to four independent networks
- One Form A solid-state contact output can provide a single contact closure or a repeating contact closure of configurable closure duration and period
- One Form C mechanical alarm contact notifies users of a major or minor event
- One standard power supply: 24–48 Vdc or 125–250 Vdc or Vac, optional second supply
- Satellite signal verification with SEL-9524B GPS/GLONASS GNSS Antenna
- LCD multi-information display plus LEDs for status
- HTTPS Web interface with SkyView, support for DHCP, LDAP, syslog, SNMP read and traps, and ACSELERATOR QuickSet[®] SEL-5030 Software
- Standard SEL 10-year warranty

Applications

Time Synchronization of Substations

The SEL-2488 has eight BNC ports, which can be configured for demodulated IRIG-B, time pulse, or modu-

lated IRIG-B (as many as four ports). Demodulated IRIG-B provides time output for protection applications, synchronizing relays, phasor measurement units, and other intelligent electronic devices (IEDs) to within

±40 ns average accuracy to UTC. Time synchronization is also essential for sequence of events recording, disturbance recording, and power system fault location.

Modulated IRIG-B can be configured for as many as four BNC outputs for synchronizing legacy devices. The DB-9 port can be used with SEL-2812 Fiber-Optic Transceivers With IRIG-B or SEL-3405 High-Accuracy IRIG-B Fiber-Optic Transceivers to send IRIG-B over long distances via a fiber-optic cable.

Ethernet ports can use NTP to distribute time to devices on the substation local-area network (LAN), such as servers, computers, and other devices that set their time through NTP or the Simple Network Time Protocol (SNTP). The SEL-2488 can serve NTP to four independent networks. The SEL-2488 can act as a stratum 1 time server with typical client synchronization accuracy to the SEL-2488 NTP server on a LAN of 0.5–2 ms. With syslog support, all SEL-2488 event information, including diagnostic and status events, is available over Ethernet in a standardized format.

The SEL-2488 Ethernet ports support hardware time stamping, enabling support of the Precision Time Protocol, PTP, defined by IEEE 1588, with purchase of a firmware upgrade.




Figure 2 Functional Diagram for Utility Substation Time Synchronization

GNSS Vulnerability Mitigation

If GNSS time signals become unavailable as a result of solar flares, jamming, or an antenna failure, the SEL-2488 switches its time source to the standard TCXO

holdover accuracy of 36 μ s after 24 hours at constant temperature, or to the optional OCXO holdover accuracy of 5 μ s after 24 hours at constant or varied temperature. In the case of a GPS spoofing attack, in which a satellite system receiver locks to a counterfeit signal, the SEL-2488 and SEL-9524B GPS/GLONASS GNSS Antenna use signals from the GLONASS Satellite constellation to validate GPS signals and identify mismatches in timing information caused by these attacks.




Figure 3 SEL-2488 Satellite Signal Verification

Cable Delay Compensation

The SEL-2488 preserves accuracy by providing time-delay compensation for antenna cables and output cables on a per-port basis with demodulated IRIG-B and pulse outputs.

The cable delay compensation of the SEL-2488 ensures high-accuracy time distribution in large facilities with dispersed IEDs or in installations where antennas must be mounted high on towers. The SEL-2488 supports as long as 500 ft of LMR-400 cable for an antenna and as long as 500 ft of RG-58 for the output cable.

Figure 4 shows an example of a clock with an antenna and two output ports. One output port is configured for 30 ns of cable delay compensation and the other is configured for 180 ns.




Figure 4 SEL-2488 Cable Delay Compensation

Configuration

HTTPS Device Webpage



Figure 5 SEL-2488 Dashboard With SkyView

The Captive Port feature on the SEL-2488 provides a DHCP server and limited DNS resolver for an easy initial connection to the device webpage for configuration. Secure access is controlled through X.509 certificates, user-based accounts, LDAP authentication, and complex passwords. The SEL device webpage includes a dashboard display of satellite signals for both GPS and GLONASS satellites. Bar charts indicate signal strengths, and the SkyView displays the present satellite overhead positions, useful information for troubleshooting potential signal and antenna installation issues.

QuickSet

QuickSet can be used for secure configuration of the SEL-2488. QuickSet is an easy-to-use, powerful tool with template design capabilities for consistent configuration of settings across multiple devices.




Figure 6 QuickSet Template for the SEL-2488

Diagrams and Dimensions




Figure 7 SEL-2488 Front and Rear Panels




Figure 8 Dimensions for Rack- and Panel-Mount Models

Specifications

Compliance

Designed and manufactured under an ISO 9001 certified quality management system

47 CFR 15B, Class A

Note: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to Part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area may be likely to cause harmful interference in which case the user will be required to correct the interference at his own expense. Any changes or modifications not expressly approved by the manufacturer can void the user's authority to operate the equipment.

UL Listed to U.S. and Canadian safety standards (File E220228; NRAQ, NRAQ7)

CE Mark

UKCA Mark

General

Receiver

Satellite Tracking: GPS L1, C/A Code (1575.42 MHz), GLONASS L1 (1602 MHz), track as many as 16 satellites for each constellation

Acquisition Times

Warm Start: 240 s (with saved almanac data)

Cold Start: 240 s + UTC compensation time (as many as 12.5 minutes)

Clock Accuracy (to UTC)

1 PPS: ± 40 ns average, ± 100 ns peak

Demodulated IRIG-B: ± 40 ns average, ± 100 ns peak

Modulated IRIG-B: ± 1 μ s peak

PTP Time-Stamp Accuracy: ± 100 ns peak

NTP Time-Stamp Accuracy (Typical): < 100 μ s

Typical client synchronization accuracy to the SEL-2488 NTP server on a LAN is 0.5–2 ms. Actual accuracy depends on network conditions.

Holdover Accuracy After 24 Hours (Typical)

TCXO: 36 μ s, constant temperature
315 μ s, $\pm 1^\circ\text{C}$

OCXO: 5 μ s, constant temperature
5 μ s, varied temperature

Note: Holdover accuracy values assume the device has been in operation for 24 hours or longer prior to holdover.

Antenna Requirements

5 V, < 80 mA
 ≥ 32 dB preamp

Electrical Output Drive Levels

Demodulated IRIG-B/PPS,
TTL (OUT1–OUT8): 5 V, 250 mA max

Modulated IRIG-B,
(OUT1–OUT4): 6.2 Vpp nominal

DB-9 Port IRIG-B output,
TTL (Pin 4/Pin 6): 5 Vdc, 5 mA

Operating Environment

Pollution Degree: 2

Overvoltage Category: II

Dimensions

1U Rack Mount

Height: 43.7 mm (1.72 in)

Depth: 248.6 mm (9.79 in)

Width: 482.5 mm (19.0 in)

1U Panel Mount:

Height: 80.0 mm (3.15 in)

Depth: 248.8 mm (9.80 in)

Width: 502.9 mm (19.80 in)

Weight

1.96 kg (4.3 lb)

Warranty

10 years

Network Management

HTTPS Web User Interface
ACSELERATOR QuickSet SEL-5030 Software
Settings Import/Export

User-Based Accounts

Maximum Local Accounts: 256

User Roles: Administrator, Engineer, User Manager, Monitor

Password Length: 1–72 characters

Password Set: All printable ASCII characters

Note: If complex passwords are enabled, the password must have at least 8 characters with at least one digit, uppercase, lowercase, and special character.

Syslog

Storage for 60,000 local syslog messages

Support for three remote syslog destinations

Simple Network Management Protocol (SNMP)

Monitors diagnostics through SNMP v2c and v3 read operations

Sends notifications using SNMP v2c traps

Support for as many as three trap servers

Network Time Protocol (NTP)

Implements NTPv4 Server, Broadcast, and Multicast formats

Precision Time Protocol (PTP)

Implements the following IEEE 1588-2008 profiles:

Default UDP (Annex D and J)
Default 802.3 (Annex F and J)
IEEE C37.238-2011
IEEE C37.238-2017
IEC/IEEE 61850-9-3:2016

Parallel Redundancy Protocol (PRP)

Implements IEC 62439-3:2016

Supports as many as two Doubly Attached Node implementing PRP (DANP) interfaces for separate PRP networks using the following physical Ethernet port combinations:

ETH 1 and ETH 2
ETH 3 and ETH 4

Supports PTP as a Doubly Attached Clock (DAC) on ports where PRP is enabled.

Active-Backup Port Bonding

Implements Active-Backup port bonding (also known Failover) using the following physical Ethernet port combinations:

ETH 1 and ETH 2
ETH 3 and ETH 4

Communications Ports

Ethernet Ports

Ports:	4 rear, 1 front
Data Rate:	10 or 100 Mbps
Front Connector:	RJ45 Female
Rear Connectors:	RJ45 Female or LC Fiber (single-mode or multimode)
Standard:	IEEE 802.3

Fiber-Optic Ports

Multimode Option (to 2 km)

Maximum TX Power:	−14 dBm
Minimum TX Power:	−20 dBm
RX Sensitivity:	−31 dBm
System Gain:	11 dB
Source:	LED
Wavelength:	1310 nm
Connector Type:	LC (IEC 61754-20)

Single-Mode Option (to 15 km)

Maximum TX Power:	−8 dBm
Minimum TX Power:	−15 dBm
RX Sensitivity:	−28 dBm
System Gain:	13 dB
Source:	Laser
Wavelength:	1310 nm
Connector Type:	LC (IEC 61754-20)

Alarm Output

Pilot Duty Rating (Per UL 508):	B300, R300
Power Supply Burden:	<0.5 W max
Rated Operational Voltage:	24–250 Vdc
Contact Protection:	270 Vdc, MOV protected
Continuous Carry:	2 A
Pickup Time:	≤8 ms typical
Dropout Time:	≤8 ms typical

Timing Output

Power Supply Burden:	<0.5 W max
Rated Operational Voltage:	12–250 Vdc
Contact Protection:	330 Vdc (250 Vac), MOV protected

Continuous Carry:	100 mA
Off Resistance:	5 MΩ
Minimum Voltage:	12 Vdc
Timing Accuracy (Closing):	±1 μs (applies only to dc voltages)

Terminal Connections

Warning: When using stranded wire, use crimp ferrules to safely capture all wire strands before assembling and attaching the plug or ground wire.

Power Supply Compression Screw Terminals

Part Number:	Use SEL P/N 420-0219 (provided)
Tightening Torque:	0.5–0.6 Nm (4–5 in-lb)
Insulation Ratings:	300 V, 90°C (194°F), minimum
Wire Material:	Copper
Size:	12–18 AWG (4.00–0.75 mm ²)

Alarm and Timing Contact Compression Screw Terminal

Part Number:	Use SEL P/N 420-0071 (provided)
Tightening Torque:	0.5–0.6 Nm (4–5 in-lb)
Insulation Ratings:	300 V, 90°C (194°F), minimum
Wire Material:	Copper
Size:	16–22 AWG (1.50–0.34 mm ²)

Ground Screw

Part Number:	#6 crimp ring terminal is recommended
Tightening Torque:	0.90–1.36 Nm (8–12 in-lb)
Insulation Ratings:	300 V, 90°C (194°F), minimum
Wire Material:	Copper
Size:	12–18 AWG (4.00–0.75 mm ²)
Length:	<3.0 m (<9.8 ft)

Power Supply

125–250 Volt Power Supply (SEL-9330-A)

Rated Supply Voltage:	125–250 Vdc 120–240 Vac, 50/60 Hz
Input Voltage Range:	88–300 Vdc or 85–264 Vac
Burden:	AC: <75 VA, 700 mA DC: <45 W
Input Voltage Interruptions:	50 ms @ 125 Vac/Vdc 100 ms @ 250 Vac/Vdc
Peak Inrush:	8 A
Internal Fuse Rating:	2.5 A, 250 Vdc/300 Vac time-lag T, 250 Vac/1500 A break rating

Note: Fuses are not user-serviceable.

24–48 Volt Power Supply (SEL-9330-C)

Rated Supply Voltage:	24–48 Vdc (polarized)
Input Voltage Range:	19.2–60.0 Vdc
Burden:	<42W, 1.7 A
Input Voltage Interruptions:	50 ms @ 48 Vdc 10 ms @ 24 Vdc
Peak Inrush:	18 A
Internal Fuse Rating:	4.0 A, 150 Vdc time-lag T, 250 Vac/1500 A break rating

Note: Fuses are not user-serviceable.

Recommended External Overcurrent Protection

Breaker Type:	Standard
Breaker Rating:	15 A at 250 Vdc
Current Breaking Capacity:	10 kA
Grounded Neutral Systems:	Device in series with the HOT or energized conductor
DC and Isolated Systems:	Device in series with both conductors

Environmental

Temperature

Operating: -40° to $+85^{\circ}\text{C}$ (-40° to $+185^{\circ}\text{F}$)

Note: UL Ambient $+40^{\circ}\text{C}$ ($+104^{\circ}\text{F}$). See *Safety Information* in the *SEL-2488 Satellite-Synchronized Network Clock Instruction Manual* for additional details.

Non-operating (storage): -40° to $+85^{\circ}\text{C}$ (-40° to $+185^{\circ}\text{F}$)

Relative Humidity

0% to 95% noncondensing

Altitude

2000 m

Type Tests

Communication Product Testing

Communications for Substation Equipment:	IEEE 1613-2009 Class 2
Power Frequency Disturbances:	IEC 61850-3:2002; Section 5.7.3

Electromagnetic Compatibility General

Measuring Relays and Protection Equipment:	IEC 60255-26:2013
--	-------------------

Electromagnetic Compatibility Emissions

IEC 60255-25:2000
IEC 60255-26:2013
CISPR 11:2009 + A1:2010
CISPR 22:2008
Canada ICES-001 (A) / NMB-001 (A)
47 CFR Part 15.107 and 109
Severity Level: Class A

Electromagnetic Compatibility Immunity

Conducted RF Immunity:	IEC 60255-22-6:2001 IEC 61000-4-6:2008 Severity Level: 10 Vrms
Radiated RF Immunity:	IEC 60255-22-3:2007 IEC 61000-4-3:2008 Severity Level: 10 V/m IEEE C37.90.2-2004 Severity Level: 35 V/m
Electrostatic Discharge Immunity:	IEC 60255-22-2:2008 IEC 61000-4-2:2008 Severity Level: $\pm 2, 4, 6, 8$ kV contact; $\pm 2, 4, 8, 15$ kV air IEEE C37.90.3-2001 Severity Level: $\pm 2, 4$, and 8 kV contact; $\pm 4, 8$, and 15 kV air
Surge Withstand Capability:	IEC 60255-22-1:2007 Severity Level: ± 2.5 kV peak common mode, ± 1.0 kV peak differential mode IEEE C37.90.1-2002 Severity Level: ± 2.5 kV, 1 MHz oscillatory; ± 4 kV, 2.5 kHz fast transient

Fast Transient/Burst Immunity:

IEC 60255-22-4:2008
IEC 61000-4-4:2011
Severity Level: ± 4 kV, 5 kHz; ± 2 kV, 5 kHz on communications ports

Surge Immunity:

IEC 60255-22-5:2008
IEC 61000-4-5:2005
Severity Level: ± 0.5 kV, 1 kV line-to-line, ± 0.5 kV, 2 kV line-to-earth; ± 0.5 kV, 1 kV line-to-earth on communications ports

Power Frequency Magnetic Field Immunity:

IEC 61000-4-8:2009
Severity Level: 1000 A/m for 3 seconds, 100 A/m for 1 minute

Pulse Magnetic Field Immunity:

IEC 61000-4-9:2001
Severity Level: 1000 A/m

Damped Oscillatory Magnetic Field Immunity:

IEC 61000-4-10:2001
Severity Level: 100 A/m (at 1 kHz and 1 MHz)

Power Supply Immunity:

IEC 60255-11:2008
IEC 61000-4-11:2004
IEC 61000-4-17:2002
IEC 61000-4-29:2000

Environmental

Cold:

IEC 60068-2-1:2007
Severity Level: 16 hours at -40°C

Damp Heat, Cyclic:

IEC 60068-2-30:2005
Severity Level: 25° to 55°C , 6 cycles, relative humidity: 95%

Dry Heat:

IEC 60068-2-2:2007
Severity Level: 16 hours at $+85^{\circ}\text{C}$

Free Fall:

IEEE 1613-2009
Severity Level: 100 mm

Vibration:

IEC 60255-21-1:1988
Severity Level:
Class 2 Endurance
Class 2 Response

Shock & Bump:

IEC 60255-21-2:1998
Severity Level:
Class 1 Shock Withstand
Class 1 Bump
Class 2 Shock Response

Seismic:

IEC 60255-21-3:1993
Severity Level:
Class 2 (Quake Response)

Safety

Measuring Relays and Protection Equipment:	IEC 60255-27:2013
Protection IP Code:	IEC 60529:2001 IP Code: IP3X for category 2 equipment
Insulation Coordination:	IEC 60255-5:2000 IEEE C37.90-2005 Dielectric (HiPot) Severity Level: Power Supply: 3100 Vdc Alarm Contact: 2500 Vac IRIG-B Input: 2100 Vdc Ethernet Ports: 1500 Vac Timer Contact (OUT1): 3500 Vdc Impulse Severity Level: 5 J; ± 5 kV, $1.2/50$ μs
Electrical Equipment for Measurement, Control, and Laboratory Use:	IEC 61010-1:2010/AMD1:2016/ COR:2019 UL 61010-1:2019, C22.2 No. 61010-1:12 IEC 61010-2:201:2017 UL 61010-2-201:2018, C22.2 No. 61010-2-201:14

Technical Support

We appreciate your interest in SEL products and services. If you have questions or comments, please contact us at:

Schweitzer Engineering Laboratories, Inc.
2350 NE Hopkins Court
Pullman, WA 99163-5603 U.S.A.
Tel: +1.509.338.3838
Fax: +1.509.332.7990
Internet: selinc.com/support
Email: info@selinc.com

Notes

© 2014–2024 by Schweitzer Engineering Laboratories, Inc. All rights reserved.

All brand or product names appearing in this document are the trademark or registered trademark of their respective holders. No SEL trademarks may be used without written permission. SEL products appearing in this document may be covered by U.S. and Foreign patents.

Schweitzer Engineering Laboratories, Inc. reserves all rights and benefits afforded under federal and international copyright and patent laws in its products, including without limitation software, firmware, and documentation.

The information in this document is provided for informational use only and is subject to change without notice. Schweitzer Engineering Laboratories, Inc. has approved only the English language document.

This product is covered by the standard SEL 10-year warranty. For warranty details, visit selinc.com or contact your customer service representative.

SCHWEITZER ENGINEERING LABORATORIES, INC.

2350 NE Hopkins Court • Pullman, WA 99163-5603 U.S.A.

Tel: +1.509.332.1890 • Fax: +1.509.332.7990

selinc.com • info@selinc.com



* P D S 2 4 8 8 - 0 1 *